

Polymer Plates

Standard & Long-Life Polymer Plates

For small to medium-sized printing runs, polymer printing plates are used which, with careful handling, permit several thousand printing operations.

Teca-Print recommends the standard printing plates for small runs, and the long-life printing plates for medium-sized runs. For sealed inking systems, we recommend the use of long-life plates.

Standard- as well as long-life plastic plates are available from stock, both in water and alcohol washable versions.

You will find the different plate types and the processing instructions on the other side.



Remove protective sheet



Expose plate under screen fit



Do not expose to the moisture and/or in the drying cabinet.



Place the deburred positive film with the coating downwards, accurate and expose.



Wash plate



Drying in the drying cabinet or oven at the prescribed temperature



Remove positive film, place deburred screen fit in position with coating downwards, and accurate.



Dry the plate with compressed air jet.

Screens for polymer plate	
Designation:	S 1512 with 120 points per cm.
Dimensions:	100 x 100 mm Art. No.: 90-00 23
Dimensions:	100 x 600 mm Art. No.: 90-00 24

Polymer Plates

Standard & Long-Life Polymer Plates